



5031



Rocker push-button NO contact Module insert

Technical Features

Electric current

| | |
|---------------------------|------|
| Switching current | 10 A |
| Momentary contact current | 10 A |

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Architecture

| | |
|---------------------------|--------|
| Control/operation element | Rocker |
| Number of poles | 1 |

Materials

| | |
|-------------|------------------|
| Material | Metal Plastic |
| Transparent | No |

Dimensions

| | |
|------------------------------------|----------|
| Height | 70.80 mm |
| Width | 70.80 mm |
| Depth | 41.60 mm |
| Built-in depth | 30 mm |
| Built-in depth flush-mounted boxes | 35 mm |

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Controls and indicators

| | |
|------------------------------|--------------------|
| Number of buttons | 1 |
| Type of push button | Single push button |
| With feedback signal contact | No |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
| Impact resistance IK | IK07 |

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Texts

| | |
|--------------------|-------------------------------------|
| Imprint | Without imprint |
| Installation mode | With spreader claws |
| Lighting | For lighting and monitoring circuit |
| Switch mode | Normally open contact |
| Type of connection | With plug-in terminals |