



JVC2400S16TW

160A TPN board, INVICTA, 24P Chassis, ISO-STD-GR

Technical Features

Connection

| | |
|-----------------------------|----|
| Number of accessible phases | 24 |
|-----------------------------|----|

Installation, mounting

| | |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

Electric current

| | |
|---|-------|
| Rated current | 160 A |
| Breaking and opening capacity I _{dm} | 0 kA |

Equipment

| | |
|------------------------|--------------------|
| With lock | Yes |
| Has mounting plate | No |
| Equipped with switch | Isolator |
| Number of switches | 1 |
| Type of busbar chassis | Fixed load chassis |

Capacity

| | |
|-------------------|----|
| Number of modules | 16 |
|-------------------|----|

Dimensions

| | |
|--------|--------|
| Height | 800 mm |
| Width | 480 mm |
| Depth | 135 mm |

Cover, door

| | |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

Materials

| | |
|----------|------------|
| Material | Steel |
| RAL code | 7035 |
| Colour | Light grey |

Safety

| | |
|-------------------------------|-----------------------|
| Protection class | Isolation class I |
| Impact resistance IK | IK05 |
| Ingress Protection (IP) class | IP30 |
| Locking type | Key lock With lock |

Architecture

| | |
|-----------------|----|
| Number of poles | 24 |
|-----------------|----|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |