



MT263A

**MCB 2P 6kA B-63A 2M**

**Technical Features**

**Electric current**

Rated current	63 A
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 400 V AC IEC 60947-2	6 kA
Rated current -15°C	78.10 A
Rated current -10°C	76.60 A
Rated current -5°C	75 A
Rated current at 0°C	73.40 A
Rated current 5°C	71.80 A
Rated current 10°C	70.10 A
Rated current 15°C	68.40 A
Rated current at 20°C	66.70 A
Rated current 25°C	64.90 A
Rated current 30°C	63 A
Rated current 35°C	62.80 A
Rated current at 40°C	62.60 A
Rated current at 45°C	62.30 A
Rated current at 50°C	62.10 A
Rated current 55°C	61.90 A
Rated current 60°C	61.70 A
Rated current 65°C	61.40 A
Rated current 70°C	61.20 A

**Architecture**

Type of pole	2P
Curve	B

**Capacity**

Number of modules	2
-------------------	---

**Main electrical attributes**

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	6 kA
-----------------------------------------------------------------------------------	------

**Installation, mounting**

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

**Voltage**

Rated operational voltage U <sub>e</sub>	400 - 400 V
Rated insulation voltage U <sub>i</sub>	500 V
Rated impulse withstand voltage U <sub>imp</sub>	4000 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Connection**

Cross-section of input and output with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for flexible conductors	1 - 25 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 35 mm <sup>2</sup>
Cross-section flexible conductor	1 - 25 mm <sup>2</sup>
Cross-section rigid conductor	1 - 35 mm <sup>2</sup>

**Installation, mounting**

Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

---

**Safety**

Ingress Protection (IP) class	IP20
Grid distance	60 mm

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	2
Air humidity protection	For all climates
Operating temperature	-25 - 70 °C

**Power**

Total power loss under IN	12 W
---------------------------	------

**Connectivity**

Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal
Type of connection	Screw terminal

**Dimensions**

Height	83 mm
Width	35 mm
Depth	70 mm

**Sustainability**

RoHS conform	Yes
--------------	-----