



HR502

Earth Leakage Relay 0.3A instantaneous Trip Type A

Technical Features

Electric current

| | |
|--|--------------|
| Rated residual operating current I _{dn} | 300 mA |
| Toroid's: Allowed overload | 30 kA/100 ms |

Safety

| | |
|-----------------------|------|
| Residual current type | A HI |
|-----------------------|------|

Equipment

| | |
|---------------------------|-----|
| With earth leakage toroid | Yes |
|---------------------------|-----|

Settings

| | |
|--------------------------------|-----|
| Time delay of residual current | 0 s |
| Adjustable time delay | No |

Dimensions

| | |
|--|----------------------------|
| Maximum connection distance between receiver and transmitter | 25 m und 50 m twisted pair |
|--|----------------------------|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |