



JVC2400S16TW

### 160A TPN board, INVICTA, 24P Chassis, ISO-STD-GR

#### Technical Features

##### Connection

|                             |    |
|-----------------------------|----|
| Number of accessible phases | 24 |
|-----------------------------|----|

##### Installation, mounting

|             |                  |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

##### Electric current

|                                   |       |
|-----------------------------------|-------|
| Rated current                     | 160 A |
| Breaking and opening capacity Idm | 0 kA  |

##### Equipment

|                        |                    |
|------------------------|--------------------|
| With lock              | Yes                |
| Has mounting plate     | No                 |
| Equipped with switch   | Isolator           |
| Number of switches     | 1                  |
| Type of busbar chassis | Fixed load chassis |

##### Capacity

|                   |    |
|-------------------|----|
| Number of modules | 16 |
|-------------------|----|

##### Dimensions

|        |        |
|--------|--------|
| Height | 800 mm |
| Width  | 480 mm |
| Depth  | 135 mm |

##### Cover, door

|                           |    |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

##### Materials

|          |            |
|----------|------------|
| Material | Steel      |
| RAL code | 7035       |
| Colour   | Light grey |

##### Safety

|                               |                       |
|-------------------------------|-----------------------|
| Protection class              | Isolation class I     |
| Impact resistance IK          | IK05                  |
| Ingress Protection (IP) class | IP30                  |
| Locking type                  | Key lock<br>With lock |

##### Architecture

|                 |    |
|-----------------|----|
| Number of poles | 24 |
|-----------------|----|

##### Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |