



HR522

### EARTH LEAKAGE RELAY 0.03-10A TIME DELAY 50% LED TEST

#### Technical Features

##### Electric current

Rated residual operating current  $I_{dn}$

30 mA
100 mA
300 mA
500 mA
1000 mA
3000 mA
10000 mA

Toroid's: Allowed overload

30 kA/100 ms

#### Safety

Residual current type

A

#### Equipment

With earth leakage toroid

Yes

#### Settings

Adjustable time delay

Yes

#### Dimensions

Maximum connection distance between receiver and transmitter

25 m und 50 m twisted pair

#### Sustainability

Halogen free

Yes

REACH-SVHC free

Yes

RoHS conform

Yes