



HR500

**Earth Leakage Relay 0.03A instantaneous Trip Type A**

**Technical Features**

**Electric current**

Rated residual operating current $I_{dn}$	30 mA
Toroid's: Allowed overload	30 kA/100 ms

**Safety**

Residual current type	A
-----------------------	---

**Equipment**

With earth leakage toroid	Yes
---------------------------	-----

**Settings**

Time delay of residual current	0 s
Adjustable time delay	No

**Dimensions**

Maximum connection distance between receiver and transmitter	25 m und 50 m twisted pair
--	----------------------------

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes