



FWB51GS

FWB encl. univers,surface mount.,IP44,classII,w. transp.door,800x300x161mm,QC

**Technical Features**

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Surface mounting

**Electric current**

Rated current	125 A
---------------	-------

**Equipment**

Number of rails	5
Number of rows	5
Number of section in width	1
With lock	No
Has neutral terminal block	Yes

**Capacity**

Number of modules	60
-------------------	----

**Functions**

With conduit inlets	Yes
---------------------	-----

**Dimensions**

Height	800 mm
Width	300 mm
Depth	165 mm

**Cover, door**

Number of cabinet doors	1
Number of locks	1

**Dimensions**

Number of width units	12
-----------------------	----

**Cover, door**

Type of handle	Latch
Door/cover is transparent	Yes

**Connection**

Number of conduit inlets	4
--------------------------	---

**Materials**

Material	Steel
RAL code	9010
Colour	Pure white

**Equipment**

Has earthing terminal block	Yes
Has mounting plate	No

**Safety**

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP44

**Sustainability**

RoHS conform	Yes
--------------	-----