



SBN333

**3-pole, 32A Modular Switch with big terminals**

**Technical Features**

**Architecture**

|                  |                 |
|------------------|-----------------|
| Number of poles  | 3               |
| Neutral position | Without neutral |
| Type of pole     | 3P              |

**Electric current**

|  |                              |
|--|------------------------------|
| Rated current  | 32 A                         |
| Acceptable current rating AC21 category A  | 32 A                         |
| Acceptable current rating AC21 category B  | 32 A                         |
| Acceptable current rating AC22 category A  | 32 A                         |
| Acceptable current rating AC22 category B  | 32 A                         |
| Rated short-circuit making capacity $I_{cm}$ under 415 V AC according to IEC 60947-3     | 0.67 kA                      |
| Rated short-time withstand current $I_{cw}$ 1s IEC 60947                                 | 0.48 kA                      |
| Rated conditional short-circuit current $I_{nc}$ with fuse according to IEC/EN 60069-2-4 | 6000A/80A gG parallel 32A gG |

**Installation, mounting**

|                           |                |
|---------------------------|----------------|
| Nominal tightening torque | 2.80 - 2.80 Nm |
|---------------------------|----------------|

**Voltage**

|                                 |             |
|---------------------------------|-------------|
| Rated operational voltage $U_e$ | 400 - 400 V |
| Type voltage supply             | AC          |
| Rated insulation voltage $U_i$  | 440 V       |

**Installation, mounting**

|   |                |
|---|----------------|
| Type of bottom connection for modular devices | Screw terminal |
|---|----------------|

**Voltage**

|   |        |
|---|--------|
| Rated impulse withstand voltage $U_{imp}$ | 6000 V |
|---|--------|

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 3 |
|-------------------|---|

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

**Frequency**

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

**Dimensions**

|            |               |
|------------|---------------|
| Height     | 83 mm         |
| Width      | 52.50 mm      |
| Depth      | 68 mm         |
| Dimensions | 83 x 52.50 mm |

**Equipment**

|                       |   |
|-----------------------|---|
| Number of NO contacts | 3 |
| Number of NC contacts | 0 |

**Use conditions**

|                               |             |
|-------------------------------|-------------|
| Operating temperature         | -20 - 70 °C |
| Storage/transport temperature | -40 - 80 °C |

**Connection**

|                                  |                          |
|----------------------------------|--------------------------|
| Cross-section flexible conductor | 2.5 - 16 mm <sup>2</sup> |
| Cross-section rigid conductor    | 2.5 - 25 mm <sup>2</sup> |

# Product Datasheet

## SBN333

---

### **Endurance**

|   |       |
|---|-------|
| Number of mechanical operations                                   | 60000 |
| Electrical durability at nominal load in AC21 in operating cycles | 5000  |
| Electrical durability at nominal load in AC22 in operating cycles | 5000  |

### **Power**

|                           |        |
|---------------------------|--------|
| Total power loss under IN | 3.50 W |
| Power loss per pole at In | 1.20 W |

### **Connectivity**

|   |                  |
|---|------------------|
| Down connection alignment for modular devices | Shifted terminal |
| Top connection alignment for modular devices  | Shifted terminal |

### **Sustainability**

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|