



LNH1250M

**HRC LV fuse NH1 gG AC500V250A double indicator with live gripping-lugs**

**Technical Features**

**Architecture**

|       |    |
|-------|----|
| Curve | gG |
|-------|----|

**Fuse**

|                      |     |
|----------------------|-----|
| Fuse size            | NH1 |
| Fuse characteristics | gG  |

**Voltage**

|                              |             |
|------------------------------|-------------|
| Type voltage supply          | AC/DC       |
| Rated operational voltage Ue | 500 - 500 V |
| Rated voltage at AC 50 Hz    | 500 - 500 V |

**Electric current**

|               |       |
|---------------|-------|
| Rated current | 250 A |
|---------------|-------|

**Use conditions**

|           |    |
|-----------|----|
| Insulated | No |
|-----------|----|

**Main electrical attributes**

|   |        |
|---|--------|
| Rated short-circuit breaking capacity Icn AC according to IEC 60898-1 | 120 kA |
|---|--------|

**Power**

|                           |      |
|---------------------------|------|
| Total power loss under IN | 20 W |
|---------------------------|------|

**Dimensions**

|        |          |
|--------|----------|
| Height | 64.50 mm |
| Width  | 135 mm   |
| Depth  | 135 mm   |

**Sustainability**

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |