



**125A TP&N BOARD 6+4WAY Surface enclosure**

**Technical Features**

**Installation, mounting**

|             |                  |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

**Electric current**

|   |      |
|---|------|
| Breaking and opening capacity I <sub>dm</sub> | 0 kA |
|---|------|

**Equipment**

|                        |               |
|------------------------|---------------|
| Has mounting plate     | No            |
| Equipped with switch   | No switch     |
| Number of switches     | 0             |
| Type of busbar chassis | Split chassis |

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 0 |
|-------------------|---|

**Dimensions**

|        |        |
|--------|--------|
| Height | 720 mm |
| Width  | 445 mm |
| Depth  | 125 mm |

**Cover, door**

|                           |    |
|---------------------------|----|
| Number of cabinet doors   | 1  |
| Door/cover is transparent | No |

**Materials**

|          |            |
|----------|------------|
| Material | Steel      |
| RAL code | 9002       |
| Colour   | Grey white |

**Safety**

|                               |                              |
|-------------------------------|------------------------------|
| Protection class              | Isolation class I            |
| Impact resistance IK          | IK05                         |
| Ingress Protection (IP) class | IP41                         |
| Locking type                  | Special tool<br>Without lock |

**Architecture**

|                 |    |
|-----------------|----|
| Number of poles | 18 |
|-----------------|----|

**Sustainability**

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|