



20317103



Temp. cont., NCcontact, centre plate, 24V AC/DC, rocker switch, K.5, al.m.lacq.

#### Technical Features

##### Architecture

Control/operation element	Rotative
---------------------------	----------

##### Electric current

Rated current	4 A
Max. switching current	10 A

##### Voltage

Nominal voltage	24 - 24 V
-----------------	-----------

##### Power supply

Supply voltage	24 V AC/DC
----------------	------------

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Settings

Comfort temperature setpoint	5 - 30 °C
------------------------------	-----------

##### Materials

Colour	Aluminium
RAL code	9006
Surface finish	Matt
Material	Metal Plastic

##### Dimensions

Height	71 mm
Width	71 mm
Depth	50.90 mm

##### Screen

With display	No
--------------	----

##### Equipment

Switching temperature difference	0.50 K
Type of thermostat	Room thermostat
Type of probe	Bimetal

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Connection

Type of contacts	1NC
------------------	-----

##### Compatibility

Type of HVAC control	Heating
----------------------	---------

##### Use conditions

Energy efficiency class	I (1%)
-------------------------	--------

##### Texts

Installation mode	Without spreader claws
Type of connection	With plug-in terminals
Thermal re-circulation	With thermal return
Imprint	With imprint
Junction	With separate connection for night lowering

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes