



LVSG00SP

NH Fuse-Switch vertical design LV size 00 185mm 3pole M8

Technical Features

Electric current

Rated current	160 A
Rated conditional short-circuit current I _{cc}	120 kA
Rated conditional short-circuit current for U _e =400 V IEC 61439-1 3.8.10.4	120 kA
Acceptable current rating AC23 category B / 400V	160 A
Acceptable current rating AC22 category B / 500V	160 A
Acceptable current rating AC21 category B / 800V	63 A
Acceptable current rating AC22 category B / 690V	160 A
Rated current for U _e =400 V AC according to IEC 61439-1 5.3.2	160 A
Rated current for U _e =690 V AC according to IEC 61439-1 5.3.2	160 A
Rated current for U _e =800 V AC according to IEC 61439-1 5.3.2	63 A
Rated conditional short-circuit current for U _e =690 V IEC 61439-1 3.8.10.4	100 kA
Rated current of fuse cartridge	2 A 4 A 6 A 10 A 16 A 20 A 25 A 32 A 35 A 40 A 50 A 63 A 80 A 100 A 125 A 160 A

Fuse

Fuse size	NH00
-----------	------

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

Connection

Connector/plug type	M8 terminal
Type of terminal cover	Standard terminal cover

Architecture

Number of poles	3
Number of switchable poles	3

Use conditions

Operating temperature	-25 - 55 °C
-----------------------	-------------

Installation, mounting

Nominal tightening torque	14 - 14 Nm
Tightening torque for mounting on busbar	14 - 14 Nm

Endurance

Electric endurance in number of cycles	200
--	-----

Safety

Ingress Protection (IP) class	IP2X
-------------------------------	------

Endurance

Number of mechanical operations	1400
Total service life (mechanical and electrical endurance) IEC 60947-3 Table 4	1600

Electric current

Rated short-time withstand current I _{cw} 1s IEC 60947	5 kA
---	------

Voltage

Rated insulation voltage Ui	1000 V
Rated impulse withstand voltage Uimp	8 kV
Rated operational voltage Ue	690 - 690 V

Dimensions

Dimensions	671 x 50 mm
Distance busbars	185 mm
Height	671 mm
Depth	123 mm

Power

Total power loss under IN	22 W
Power loss of the Fuse-Link installed in device	12 W
Power loss at full load	58 W

Frequency

Frequency	50 - 60 Hz
-----------	------------

Electrical protection

With fault indicator	No
----------------------	----

Functions

Double interrupting	No
---------------------	----

Materials

Contains recycled material (% of total plastic weight)	0 %
--	-----

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes