



FWU53S

FW flush encl. 5-rows 180 modules, IP30, classII, niche 807x815x115mm

Technical Features

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Flush mounting Hollow wall

Electric current

Rated current	125 A
---------------	-------

Equipment

Number of rails	15
Number of rows	5
Number of section in width	3
With lock	No
Has neutral terminal block	Yes

Capacity

Number of modules	180
-------------------	-----

Functions

Has protection main switch	No
With conduit inlets	Yes

Dimensions

Height	853 mm
Width	853 mm
Depth	125 mm
Built-in height	802 mm
Built-in width	810 mm

Cover, door

Number of cabinet doors	2
-------------------------	---

Dimensions

Built-in depth	112 mm
Number of width units	36

Cover, door

Type of handle	Hinged pattern handle
Door/cover is transparent	No

Connection

Number of conduit inlets	6
--------------------------	---

Connectivity

Mounting type	Screw mounting
---------------	----------------

Materials

Material	Steel
RAL code	9010
Colour	Pure white

Equipment

Has earthing terminal block	Yes
Has mounting plate	No

Safety

Protection class	Isolation class II
Impact resistance IK	IK09
Ingress Protection (IP) class	IP30

Safety	
Locking type	Without lock
Glow wire test	850 °C
Sustainability	
RoHS conform	Yes