



FWU51S

**FW flush encl. 5-rows 60 modules, IP30, classII, niche 807x315x115mm**

**Technical Features**

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Flush mounting Hollow wall

**Electric current**

Rated current	125 A
---------------	-------

**Equipment**

Number of rails	5
Number of rows	5
Number of section in width	1
With lock	No
Has neutral terminal block	Yes

**Capacity**

Number of modules	60
-------------------	----

**Functions**

Has protection main switch	No
With conduit inlets	Yes

**Dimensions**

Height	853 mm
Width	353 mm
Depth	125 mm
Built-in height	802 mm
Built-in width	310 mm

**Cover, door**

Number of cabinet doors	1
-------------------------	---

**Dimensions**

Built-in depth	112 mm
Number of width units	12

**Cover, door**

Type of handle	Hinged pattern handle
Door/cover is transparent	No

**Connection**

Number of conduit inlets	2
--------------------------	---

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Materials**

Material	Steel
RAL code	9010
Colour	Pure white

**Equipment**

Has earthing terminal block	Yes
Has mounting plate	No

**Safety**

Protection class	Isolation class II
Impact resistance IK	IK09
Ingress Protection (IP) class	IP30

---

**Safety**

Locking type	Without lock
Glow wire test	850 °C

**Sustainability**

RoHS conform	Yes
--------------	-----