




HA304

Load break switch 3P 80A

Technical Features

Electric current

Rated current	80 A
Acceptable current rating AC21	80 A
Acceptable current rating AC21 category A	80 A
Acceptable current rating AC21 category B	80 A
Acceptable current rating AC22 category A	80 A
Acceptable current rating AC22 category B	80 A
Acceptable current rating AC23 category A	63 A
Acceptable current rating AC23 category B	63 A
Rated short-time withstand current I _{cs} IEC 60947	2.50 kA
Rated short-time withstand current I _{cs} IEC 60947	2.50 kA

Architecture

Type of pole	3P
Number of poles	3

Connection

Cross-section rigid conductor	50 mm ² max.
Cross-section flexible conductor	50 mm ²

Voltage

Rated insulation voltage U _i	800 V
Rated impulse withstand voltage U _{imp}	8000 V
Rated operational voltage U _e	380 - 415 V

Power

Power loss per pole at I _n	2 W
Total power loss under I _N	6.10 W
Rated operational power under 400 V AC AC1	52000 W
Rated operational power under 400 V AC AC23	28000 W

Equipment

Motor drive optional	No
Number of auxiliary contacts as change-over contact	0
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0

Use conditions

Operating temperature	-20 - 70 °C
-----------------------	-------------

Cover, door

Interlockable	Yes
---------------	-----

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Architecture

Control/operation element	Short rotary handle
---------------------------	---------------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Functions

Is reversing switch	No
Version as emergency stop installation	No
Version as main switch	Yes
Version as maintenance/service switch	Yes
Version as safety switch	Yes
Version as switch disconnecter compact	Yes

Installation, mounting		
Nominal tightening torque		6 - 6.6 Nm
Capacity		
Number of modules		6
Connectivity		
Type of connection		Screw terminal
Dimensions		
Height		86.5 mm
Width		108 mm
Depth		90 mm
Sustainability		
REACH-SVHC free		Yes
RoHS conform		Yes