



HAD310

Load break switch 3P 100A

Technical Features

Electric current

Rated current	100 A
Acceptable current rating AC21	100 A
Acceptable current rating AC21 category A	100 A
Acceptable current rating AC21 category B	100 A

Architecture

Control/operation element	Short rotary handle
---------------------------	---------------------

Electric current

Acceptable current rating AC23 category A	100 A
---	-------

Architecture

Number of poles	3
-----------------	---

Electric current

Rated short-time withstand current I _{cs} 1s IEC 60947	2.75 kA
Rated short-time withstand current I _{cs} IEC 60947	2.75 kA
Rated conditional short-circuit current I _{cc} with gI-gG fuses	25 kA

Connection

Cross-section rigid conductor	70 mm ²
-------------------------------	--------------------

Voltage

Rated insulation voltage U _i	800 V
Rated impulse withstand voltage U _{imp}	8000 V
Rated operational voltage U _e	380 - 415 V

Power

Power loss per pole at I _n	4.30 W
Total power loss under I _N	12.90 W
Rated operational power under 400 V AC AC1	65000 W
Rated operational power under 400 V AC AC23	45000 W

Installation, mounting

Nominal tightening torque	4 - 4.4 Nm
---------------------------	------------

Equipment

Motor drive optional	No
Number of auxiliary contacts as change-over contact	0
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0

Use conditions

Operating temperature	-20 - 70 °C
-----------------------	-------------

Cover, door

Interlockable	Yes
---------------	-----

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Functions

Is reversing switch	No
Version as emergency stop installation	No

Functions

Version as main switch	Yes
Version as maintenance/service switch	Yes
Version as safety switch	Yes
Version as switch disconnecter compact	Yes

Capacity

Number of modules	4.45
-------------------	------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes