



HAD312

Load break switch 3P 125A

Technical Features

Electric current

Rated current	125 A
Acceptable current rating AC21	125 A
Acceptable current rating AC21 category B	125 A
Acceptable current rating AC22 category B	125 A

Architecture

Control/operation element	Short rotary handle
---------------------------	---------------------

Electric current

Acceptable current rating AC23 category A	100 A
Acceptable current rating AC23 category B	100 A

Architecture

Number of poles	3
-----------------	---

Electric current

Rated short-time withstand current I _{cw} 1s IEC 60947	2.75 kA
Rated short-time withstand current I _{cw} IEC 60947	2.75 kA

Connection

Cross-section rigid conductor	70 mm ²
-------------------------------	--------------------

Voltage

Rated insulation voltage U _i	800 V
Rated impulse withstand voltage U _{imp}	8000 V
Rated operational voltage U _e	380 - 415 V

Power

Power loss per pole at I _n	7.10 W
Total power loss under I _N	21.30 W
Rated operational power under 400 V AC AC1	82000 W
Rated operational power under 400 V AC AC23	56000 W

Installation, mounting

Nominal tightening torque	4 - 4.4 Nm
---------------------------	------------

Equipment

Motor drive optional	No
Number of auxiliary contacts as change-over contact	0
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0

Use conditions

Operating temperature	-20 - 70 °C
-----------------------	-------------

Cover, door

Interlockable	Yes
---------------	-----

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Functions

Is reversing switch	No
Version as emergency stop installation	No
Version as main switch	Yes
Version as maintenance/service switch	Yes

Functions	
Version as safety switch	Yes
Version as switch disconnecter compact	Yes
Capacity	
Number of modules	4.45
Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes