




ADM410T

RCBO 4P 6kA C-10A 30mA A

Technical Features

Electric current

Rated current	10 A
Rated residual operating current I_{dn}	30 mA
Rated current -25°C	12.30 A
Rated current at -20°C	12.10 A
Rated current -15°C	11.90 A
Rated current -10°C	11.70 A
Rated current -5°C	11.50 A
Rated current at 0°C	11.30 A
Rated current 5°C	11.10 A
Rated current 10°C	10.90 A
Rated current 15°C	10.70 A
Rated current at 20°C	10.50 A
Rated current 25°C	10.20 A
Rated current 30°C	10 A
Rated current 35°C	9.80 A
Rated current at 40°C	9.50 A
Rated current at 45°C	9.20 A
Rated current at 50°C	9 A
Rated current 55°C	8.70 A
Rated current 60°C	8.40 A
Rated short-circuit breaking capacity I_{cn} under 230 V AC according to IEC 61009-1	6 kA

Architecture

Curve	C
Number of poles	4
Neutral position	Right
Type of pole	4P
Number of protected poles	4

Capacity

Number of modules	4
-------------------	---

Safety

Residual current type	A
Ingress Protection (IP) class	IP2X

Voltage

Type voltage supply	AC
Rated operational voltage U_e	230 - 415 V
Rated insulation voltage U_i	500 V
Dielectric strength value of power frequency	2 kV
Rated impulse withstand voltage U_{imp}	4000 V
Overvoltage category according to IEC 60947-1	3

Main electrical attributes

Rated short-circuit breaking capacity I_{cn} AC according to IEC 60898-1	6 kA
--	------

Installation, mounting

Nominal tightening torque top terminal	2 - 2 Nm
Nominal tightening torque down terminal	2 - 2 Nm

Frequency

Frequency	50 - 50 Hz
-----------	------------

Connection

Cross-section of input with screws, for flexible conductors	1 - 16 mm ²
Cross-section of input with screws, for massive conductors	1 - 25 mm ²

Installation, mounting

Nominal tightening torque	2 - 2 Nm
360° mounting position possible	Yes

Use conditions

Class of energy limitation I ² t	3
Operating temperature	-25 - 40 °C

Dimensions

Height	84 mm
Width	71 mm
Depth	70 mm

Installation, mounting

Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	biconnect Bypass

Power

Total power loss under IN	9.70 W
---------------------------	--------

Sustainability

RoHS conform	Yes
--------------	-----