



WMSS82

### 2 Gang Double Pole Switched Socket Dual Earth

#### Technical Features

##### Electric current

Rated current	13 A
---------------	------

##### Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

##### Materials

Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated

##### Dimensions

Height	86 mm
Width	146 mm
Depth	29.50 mm

##### Installation, mounting

Mounting on	Flush mounting
Mounting-/Connection Position	Horizontal

##### Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

##### Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

##### Accessories

Has labelling field	No
---------------------	----

##### Capacity

Number of modules	0
-------------------	---

##### Safety

With enhanced contact protection	No
Ingress Protection (IP) class	IP20

##### Functions

With orientation lighting	No
With function lighting	No

##### Texts

Imprint	Without imprint
Cover	Full cover plate
Wiring	With double earth connection
Protection	Enhanced contact protection

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes