Product Datasheet
SK601

SK601

Reverser 2O 2F

Technical Features

Architecture	
Number of poles	2
Type of pole	2P
Electric current	
Rated current	20 A
Rated conditional short-circuit current Icc with gl-gG fuses	8 kA
Voltage	
Rated operational voltage Ue	660 - 660 V
Type voltage supply	AC
Rated insulation voltage Ui	690 V
Capacity	
Number of modules	3
Safety	
Ingress Protection (IP) class	IP20
Frequency	
Frequency	50 - 50 Hz
Dimensions	
Height	85 mm
Width	53 mm
Depth	64 mm
Dimensions	85 x 53 mm
Equipment	
Number of NO contacts	2
Number of NC contacts	2
Use conditions	
Operating temperature	-10 - 40 °C
Storage/transport temperature	-40 - 80 °C
Connection	
Cross-section flexible conductor	1.5 - 10 mm^2
Cross-section rigid conductor	1 - 6 mm^2
Sustainability	
REACh-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings