



SK600

### Selector switch non spring ret

#### Technical Features

##### Architecture

Number of poles	1
Type of pole	1P

##### Electric current

Rated current	20 A
Rated conditional short-circuit current Icc with gl-gG fuses	8 kA

##### Voltage

Rated operational voltage Ue	660 - 660 V
Type voltage supply	AC
Rated insulation voltage Ui	690 V

##### Capacity

Number of modules	3
-------------------	---

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Frequency

Frequency	50 - 50 Hz
-----------	------------

##### Dimensions

Height	85 mm
Width	53 mm
Depth	64 mm
Dimensions	85 x 53 mm

##### Equipment

Number of NO contacts	0
Number of NC contacts	0

##### Use conditions

Operating temperature	-10 - 40 °C
Storage/transport temperature	-40 - 80 °C

##### Connection

Cross-section flexible conductor	1.5 - 10 mm <sup>2</sup>
Cross-section rigid conductor	1 - 6 mm <sup>2</sup>

##### Power

Total power loss under IN	0.70 W
---------------------------	--------

##### Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

