



HA460

### Load break switch 4P 800A

#### Technical Features

##### Electric current

Rated current	800 A
Rated short-time withstand current I <sub>cs</sub> IEC 60947	26 kA
Acceptable current rating AC21	800 A
Acceptable current rating AC21 category A	800 A
Acceptable current rating AC21 category B	800 A
Acceptable current rating AC22 category A	800 A
Acceptable current rating AC22 category B	800 A
Acceptable current rating AC23 category A	800 A
Acceptable current rating AC23 category B	800 A
Rated short-circuit making capacity I <sub>cm</sub> under 415 V AC according to IEC 60947-3	48 kA
Rated short-time withstand current I <sub>cs</sub> 1s IEC 60947	26 kA

##### Architecture

Number of poles	4
Control/operation element	Long rotary handle
Device construction type	Fixed built-in
Type of pole	4P

##### Dimensions

Height	530 mm
Width	420 mm
Depth	295 mm

##### Cover, door

Interlockable	Yes
---------------	-----

##### Safety

Ingress Protection (IP) class	IP00
-------------------------------	------

##### Connection

Cross-section rigid conductor	2x 300 mm <sup>2</sup>
Cross-section flexible conductor	2x 300 mm <sup>2</sup>

##### Voltage

Rated insulation voltage U <sub>i</sub>	1000 V
Rated impulse withstand voltage U <sub>imp</sub>	12000 V
Rated operational voltage U <sub>e</sub>	380 - 415 V

##### Power

Power loss per pole at I <sub>n</sub>	39.70 W
Total power loss under I <sub>N</sub>	199.10 W
Rated operational power under 400 V AC AC1	526000 W
Rated operational power under 400 V AC AC23	360000 W

##### Controls and indicators

Motor drive integrated	No
------------------------	----

##### Use conditions

Operating temperature	-20 - 70 °C
-----------------------	-------------

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Functions

Is reversing switch	No
Version as emergency stop installation	No
Version as main switch	Yes
Version as maintenance/service switch	Yes

**Functions**

Version as safety switch	Yes
Version as switch disconnecter compact	Yes

**Equipment**

Motor drive optional	No
Number of auxiliary contacts as change-over contact	0
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0

**Installation, mounting**

Nominal tightening torque	40 - 45 Nm
---------------------------	------------

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes