



WNA402B

**cubyko Double horizontal flush adapter white IP55**

**Technical Features**

**Capacity**

Number of gangs	2
Number of modules	2

**Materials**

Colour	Polar white
RAL code	9010
Surface finish	Matt
Material	Thermoplastic
Contains recycled material (% of total plastic weight)	0 %
Treatment	Untreated

**Dimensions**

Height	154 mm
Width	83 mm
Depth	38 mm
Height of P-touch band for labelling field	0 mm

**Accessories**

Has labelling field	No
---------------------	----

**Installation, mounting**

Mounting on	Flush mounting
Mounting-/Connection Position	Horizontal

**Safety**

Ingress Protection (IP) class	IP20
Usable in higher IP class	IP55 with closed cover
Impact resistance IK	IK05

**Use conditions**

Operating temperature	-15 - 30 °C
-----------------------	-------------

**Texts**

Installation mode	With clamp/screw fastening With mounting adapter and sealing For flush-mounted and hollow wall mounting For vertical mounting
-------------------	---

**Sustainability**

REACH-SVHC free	Yes
-----------------	-----