



ADM432T

**RCBO 4P 6kA C-32A 30mA A**

**Technical Features**

**Electric current**

Rated current	32 A
Rated residual operating current I <sub>dn</sub>	30 mA
Rated current -25°C	39.90 A
Rated current at -20°C	39.30 A
Rated current -15°C	38.60 A
Rated current -10°C	37.90 A
Rated current -5°C	37.20 A
Rated current at 0°C	36.50 A
Rated current 5°C	35.80 A
Rated current 10°C	35.10 A
Rated current 15°C	34.30 A
Rated current at 20°C	33.60 A
Rated current 25°C	32.80 A
Rated current 30°C	32 A
Rated current 35°C	31.20 A
Rated current at 40°C	30.30 A
Rated current at 45°C	29.40 A
Rated current at 50°C	28.50 A
Rated current 55°C	27.50 A
Rated current 60°C	26.50 A
Rated short-circuit breaking capacity I <sub>cn</sub> under 230 V AC according to IEC 61009-1	6 kA

**Architecture**

Curve	C
Number of poles	4
Neutral position	Right
Type of pole	4P
Number of protected poles	4

**Capacity**

Number of modules	4
-------------------	---

**Safety**

Residual current type	A
Ingress Protection (IP) class	IP2X

**Voltage**

Type voltage supply	AC
Rated operational voltage U <sub>e</sub>	230 - 415 V
Rated insulation voltage U <sub>i</sub>	500 V
Dielectric strength value of power frequency	2 kV
Rated impulse withstand voltage U <sub>imp</sub>	4000 V
Overvoltage category according to IEC 60947-1	3

**Main electrical attributes**

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	6 kA
---	------

**Installation, mounting**

Nominal tightening torque top terminal	2 - 2 Nm
Nominal tightening torque down terminal	2 - 2 Nm

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Connection**

Cross-section of input with screws, for flexible conductors	1 - 16 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 25 mm <sup>2</sup>

---

**Installation, mounting**

Nominal tightening torque	2 - 2 Nm
360° mounting position possible	Yes

---

**Use conditions**

Class of energy limitation I <sup>2</sup> t	3
Operating temperature	-25 - 40 °C

---

**Dimensions**

Height	84 mm
Width	71 mm
Depth	70 mm

---

**Installation, mounting**

Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	biconnect Bypass

---

**Power**

Total power loss under IN	14.60 W
---------------------------	---------

---

**Sustainability**

RoHS conform	Yes
--------------	-----