



ADP466H

### RCBO 4P 6kA C-20A 300mA AC

#### Technical Features

##### Electric current

Rated current	20 A
Rated residual operating current I <sub>dn</sub>	300 mA
Rated short-circuit breaking capacity I <sub>cn</sub> under 400 V AC according to IEC 60898-1	6 kA
Rated current -25°C	23.80 A
Rated current at -20°C	23.50 A
Rated current -15°C	23.20 A
Rated current -10°C	22.90 A
Rated current -5°C	22.50 A
Rated current at 0°C	22.20 A
Rated current 5°C	21.80 A
Rated current 10°C	21.50 A
Rated current 15°C	21.10 A
Rated current at 20°C	20.80 A
Rated current 25°C	20.40 A
Rated current 30°C	20 A
Rated current 35°C	19.60 A
Rated current at 40°C	19.10 A
Rated current at 45°C	18.60 A
Rated current at 50°C	18.20 A
Rated current 55°C	17.70 A
Rated current 60°C	17.20 A

##### Architecture

Curve	C
Neutral position	Left Right
Type of pole	4P
Number of protected poles	4

##### Capacity

Number of modules	4
-------------------	---

##### Safety

Residual current type	AC
Ingress Protection (IP) class	IP20

##### Voltage

Type voltage supply	AC
---------------------	----

##### Electric current

Rated service breaking capacity I <sub>cs</sub> AC according to IEC 60898-1	6 kA
---	------

##### Voltage

Rated operational voltage U <sub>e</sub>	230 - 400 V
Rated insulation voltage U <sub>i</sub>	500 V
Dielectric strength value of power frequency	2 kV
Rated impulse withstand voltage U <sub>imp</sub>	4000 V

##### Main electrical attributes

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	6 kA
---	------

##### Installation, mounting

Nominal tightening torque down terminal	2 - 2 Nm
Nominal tightening torque top terminal	2 - 2 Nm

##### Frequency

Frequency	50 - 50 Hz
-----------	------------

---

**Connection**

Cross-section of input with screws, for flexible conductors	1 - 16 mm <sup>2</sup>
Cross-section of input with screws, for massive conductors	1 - 25 mm <sup>2</sup>

---

**Installation, mounting**

Nominal tightening torque	2 - 2 Nm
360° mounting position possible	Yes

---

**Use conditions**

Class of energy limitation I <sup>2</sup> t	3
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Operating temperature	-5 - 40 °C

---

**Dimensions**

Height	84 mm
Width	71 mm
Depth	70 mm

---

**Installation, mounting**

Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	biconnect

---

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

---

**Power**

Total power loss under IN	11.70 W
---------------------------	---------

---

**Sustainability**

RoHS conform	Yes
--------------	-----