

Emerg Light Discharge Pack 3 (Wired)

Technical Features

Voltage

Command voltage for 50 Hz	230 - 230 V
---------------------------	-------------

Dimensions

Height	80 mm
Width	65 mm
Depth	110 mm

Frequency

Frequency	50 - 50 Hz
-----------	------------

Safety

Ingress Protection (IP) class	IP2X
-------------------------------	------

Materials

Material	Plastic
----------	---------

Installation, mounting

Mounting on	DIN rail
-------------	----------

Connection

Number of contacts	4
--------------------	---

Capacity

Number of modules	4
-------------------	---

Use conditions

Operating temperature	-10 - 50 °C
Storage/transport temperature	-40 - 80 °C

Electric current

Rated current	40 A
---------------	------

Compatibility

Suitable for DIN Rail	Yes
-----------------------	-----

Settings

Time delay	10 Min - 180 Min
------------	------------------

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Connection

Type of contacts	4NC
------------------	-----

Equipment

With lock	No
-----------	----

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes