



EMERG2W

Emerg Light Discharge Pack 2 (Wired)

Technical Features

Voltage

Command voltage for 50 Hz	230 - 230 V
---------------------------	-------------

Dimensions

Height	95 mm
Width	55 mm
Depth	160 mm

Frequency

Frequency	50 - 50 Hz
-----------	------------

Safety

Ingress Protection (IP) class	IP30
-------------------------------	------

Materials

Material	Plastic
----------	---------

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Connection

Number of contacts	2
--------------------	---

Equipment

Number of keys	1
----------------	---

Capacity

Number of modules	2
-------------------	---

Use conditions

Operating temperature	-10 - 50 °C
Storage/transport temperature	-40 - 80 °C

Electric current

Rated current	25 A
---------------	------

Compatibility

Suitable for DIN Rail	No
-----------------------	----

Settings

Time delay	10 Min - 180 Min
------------	------------------

Connectivity

Type of connection	Wire connection
--------------------	-----------------

Connection

Type of contacts	2NC
------------------	-----

Equipment

With lock	Yes
-----------	-----