



KB363C

Insulated busbar 3P 63A prong 10mm² 24M

Technical Features

Electric current

| | |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

Architecture

| | |
|-----------------|---|
| Number of poles | 3 |
|-----------------|---|

Dimensions

| | |
|--------|--------|
| Length | 420 mm |
|--------|--------|

Voltage

| | |
|--------------------------------------|--------|
| Rated impulse withstand voltage Uimp | 4000 V |
|--------------------------------------|--------|

| | |
|------------------------------|-------------|
| Rated operational voltage Ue | 230 - 400 V |
|------------------------------|-------------|

Connection

| | |
|-------------------------------|--------------------|
| Cross-section rigid conductor | 10 mm ² |
|-------------------------------|--------------------|

| | |
|---------------------|-----------------------|
| Connector/plug type | Phase busbar with pin |
|---------------------|-----------------------|

Capacity

| | |
|-------------------|----|
| Number of modules | 24 |
|-------------------|----|

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|