



MCN304

### MCB 3P 6kA C-4A 3M

#### Technical Features

##### Electric current

Rated current	4 A
Rated short-circuit breaking capacity Icn under 230 V AC according to IEC 60898-1	6 kA
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	10 kA
Rated current -15°C	4.7 A
Rated current -10°C	4.6 A
Rated current -5°C	4.5 A
Rated current at 0°C	4.5 A
Rated current 5°C	4.4 A
Rated current 10°C	4.3 A
Rated current 15°C	4.2 A
Rated current at 20°C	4.2 A
Rated current 25°C	4.1 A
Rated current 30°C	4 A
Rated current 35°C	3.9 A
Rated current at 40°C	3.8 A
Rated current at 45°C	3.7 A
Rated current at 50°C	3.6 A
Rated current 55°C	3.5 A
Rated current 60°C	3.4 A
Rated current 65°C	3.3 A
Rated current 70°C	3.2 A

##### Architecture

Type of pole	3P
Curve	C

##### Capacity

Number of modules	3
-------------------	---

##### Main electrical attributes

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	6 kA
---	------

##### Installation, mounting

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

##### Voltage

Rated operational voltage Ue	230 - 400 V
Type voltage supply	AC
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4000 V

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Connection

Cross-section of input and output with screws, for massive conductors	1 - 35 mm²
Cross-section of input and output with screws, for flexible conductors	1 - 25 mm²
Cross-section of input with screws, for flexible conductors	1 - 25 mm²
Cross-section of input with screws, for massive conductors	1 - 35 mm²
Cross-section flexible conductor	1 - 25 mm²
Cross-section rigid conductor	1 - 35 mm²

##### Installation, mounting

Nominal tightening torque	2.80 - 2.80 Nm
Type of bottom connection for modular devices	biconnect
Type of top connection for modular devices	Screw terminal
360° mounting position possible	Yes

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I <sup>2</sup> t	3
Air humidity protection	For all climates
Operating temperature	-25 - +70 °C

**Power**

Total power loss under IN	5.70 W
---------------------------	--------

**Connectivity**

Type of connection	Screw terminal
Top connection alignment for modular devices	Aligned terminal
Down connection alignment for modular devices	Aligned terminal

**Dimensions**

Height	83 mm
Width	52.50 mm
Depth	70 mm

**Sustainability**

RoHS conform	Yes
--------------	-----

**Illustrations | Drawings**

