

**Moulded Case Circuit Breaker h3 x160 TM FIX 3P3D 16A 25kA FTC**

**Technical Features**

**Electric current**

|   |         |
|---|---------|
| Rated current   | 16 A    |
| Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 400 V AC IEC 60947-2 | 25 kA   |
| Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 240 V AC IEC 60947-2 | 35 kA   |
| Rated service breaking capacity I <sub>cs</sub> under 230 V AC according to IEC 60947-2   | 25 kA   |
| Rated service breaking capacity I <sub>cs</sub> under 400 V AC according to IEC 60947-2   | 20 kA   |
| Rated current 10°C according to IEC 60947   | 21.50 A |
| Rated current 15°C according to IEC 60947   | 20.90 A |
| Rated current 20°C according to IEC 60947   | 20.20 A |
| Rated current 25°C according to IEC 60947   | 19.60 A |
| Rated current 30°C according to IEC 60947   | 18.90 A |
| Rated current at 35°C according to IEC 60947  | 18.20 A |
| Rated current at 40°C according to IEC 60947  | 17.50 A |
| Rated current 45°C according to IEC 60947   | 16.70 A |
| Rated current 50°C according to IEC 60947   | 16 A    |
| Rated current 55°C according to IEC 60947   | 15.10 A |
| Rated current at 60°C according to IEC 60947  | 14.20 A |
| Rated current 65°C according to IEC 60947   | 13.30 A |
| Rated current 70°C according to IEC 60947   | 12.30 A |

**Architecture**

|                  |                 |
|------------------|-----------------|
| Number of poles  | 3               |
| Neutral position | Without neutral |

**Tripping**

|                            |       |
|----------------------------|-------|
| Response time when opening | 10 ms |
|----------------------------|-------|

**Frequency**

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

**Voltage**

|  |        |
|--|--------|
| Rated impulse withstand voltage U <sub>imp</sub> | 8000 V |
| Rated insulation voltage U <sub>i</sub>          | 690 V  |

**Functions**

|           |        |
|-----------|--------|
| Trip unit | TM F/F |
|-----------|--------|

**Power**

|                                       |        |
|---------------------------------------|--------|
| Total power loss under I <sub>N</sub> | 5.30 W |
|---------------------------------------|--------|

**Endurance**

|  |       |
|--|-------|
| Electric endurance in number of cycles | 10000 |
| Number of mechanical operations        | 20000 |

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP4X |
|-------------------------------|------|

**Connection**

|                                  |                        |
|----------------------------------|------------------------|
| Cross-section flexible conductor | 4 - 70 mm <sup>2</sup> |
| Cross-section rigid conductor    | 4 - 95 mm <sup>2</sup> |

**Settings**

|   |   |
|---|---|
| Thermal protection knob setting xI <sub>N</sub> | 1 |
|   | 1 |

**Dimensions**

|        |        |
|--------|--------|
| Height | 130 mm |
| Width  | 75 mm  |
| Depth  | 68 mm  |

---

**Compatibility**

---

|                       |    |
|-----------------------|----|
| Suitable for DIN Rail | No |
|-----------------------|----|

---

**Main electrical attributes**

---

|                               |          |
|-------------------------------|----------|
| Magnetic protection trip time | 0 - 0 ms |
|-------------------------------|----------|

---

**Sustainability**

---

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|

---

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

---