



ERC625S

**Humfree Override Contactor 25A, 2NO, 230V~50/60Hz**

**Technical Features**

**Connection**

Type of contacts	2NO
------------------	-----

**Electric current**

Rated current	25 A
---------------	------

**Capacity**

Number of modules	2
-------------------	---

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Voltage**

Rated impulse withstand voltage Uimp	4000 V
--------------------------------------	--------

Rated insulation voltage Ui	440 V
-----------------------------	-------

Rated operational voltage Ue	400 - 400 V
------------------------------	-------------

Command voltage AC	230 - 230 V
--------------------	-------------

Command voltage DC	0 - 0 V
--------------------	---------

**Use conditions**

Operating temperature	-10 - 50 °C
-----------------------	-------------

**Use**

Category of use	AC-7a/AC-7b
-----------------	-------------

**Use conditions**

Storage/transport temperature	-40 - 80 °C
-------------------------------	-------------

**Endurance**

Number of mechanical operations	100000
---------------------------------	--------

**Texts**

Safety hint	Humfree contactors are not suitable for intensive use cases (powered 24/7) and in these cases industrial contactors must be used.
-------------	---

**Endurance**

Electric endurance in number of cycles	30000
--	-------

**Power**

Total power loss under IN	5.80 W
---------------------------	--------

Inrush power absorbed	2.80 VA
-----------------------	---------

**Dimensions**

Height	83 mm
--------	-------

Width	35.75 mm
-------	----------

Depth	60 mm
-------	-------

**Equipment**

Number of NO contacts	2
-----------------------	---

Number of NC contacts	0
-----------------------	---

With switch for manual switch	Yes
-------------------------------	-----

**Connection**

Cross-section flexible conductor	1 - 6 mm <sup>2</sup>
----------------------------------	-----------------------

Cross-section rigid conductor	1 - 10 mm <sup>2</sup>
-------------------------------	------------------------

**Installation, mounting**

Nominal tightening torque	1.20 - 1.20 Nm
---------------------------	----------------

**Sustainability**

RoHS conform

Yes