



WBP2S

**Premiere 10A horz twin GPO**

**Technical Features**

**Electric current**

Rated current	10 A
---------------	------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Materials**

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC) Thermoplastic
Treatment	Untreated

**Dimensions**

Height	77 mm
Width	117 mm
Depth	28 mm
Built-in depth flush-mounted boxes	23 mm
Built-in depth	11 mm

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Connectivity**

Type of connection	Screw terminal
Mounting type	Screw mounting

**Equipment**

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

**Accessories**

Has labelling field	No
---------------------	----

**Capacity**

Number of modules	2
-------------------	---

**Safety**

Impact resistance IK	IK08
Ingress Protection (IP) class	IP20

**Functions**

With orientation lighting	No
With function lighting	No

**Texts**

Imprint	Without imprint
Cover	Full cover plate
Protection	Enhanced contact protection
Type of connection	With screw terminals

**Suitable for**

premiere
----------

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes