
Product Datasheet
AFM456C



AFM456C

RCBO 4P 6kA C-6A 300mA A Class

Technical Features

Architecture	
Type of pole	4P
Number of protected poles	4
Curve	C
Electric current	
Rated current	6 A
Rated residual operating current Idn	300 mA
Rated current -25°C	7.30 A
Rated current at -20°C	7.20 A
Rated current -15°C	7.10 A
Rated current -10°C	7 A
Rated current -5°C	6.90 A
Rated current at 0°C	6.80 A
Rated current 5°C	6.60 A
Rated current 10°C	6.50 A
Rated current 15°C	6.40 A
Rated current at 20°C	6.30 A
Rated current 25°C	6.10 A
Rated current 30°C	6 A
Rated current 35°C	5.90 A
Rated current at 40°C	5.70 A
Rated current at 45°C	5.60 A
Rated current at 50°C	5.40 A
Rated current 55°C	5.30 A
Rated current 60°C	5.10 A
Correction factor of rating current for 2 devices placed side by side	0.80
Min./max. threshold value of the AC thermal operation	1.13 - 1.45 A
Safety	
Residual current type	A
Ingress Protection (IP) class	IP20
Main electrical attributes	
Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	6 kA
Voltage	
Rated insulation voltage Ui	500 V
Electric current	
Rated service breaking capacity Ics AC according to IEC 60898-1	6 kA
Voltage	
Rated impulse withstand voltage Uimp	4000 V
Rated operational voltage Ue	230 - 400 V
Overvoltage category according to IEC 60947-1	3
Type voltage supply	AC
Dielectric strength value of power frequency	2 kV
Power	
Total power loss under IN	6.80 W
Frequency	
Frequency	50 - 50 Hz
Use conditions	
Max. altitude	2000 m

Installation, mounting	
Nominal tightening torque down terminal	2 - 2 Nm
Nominal tightening torque top terminal	2 - 2 Nm
Use conditions	
Class of energy limitation I^2t	3
Endurance	
Electric endurance in number of cycles	2000
Number of mechanical operations	4000
Connection	
Cross-section of input with screws, for flexible conductors	1 - 16 mm^2
Cross-section of input with screws, for massive conductors	1 - 25 mm^2
Capacity	
Number of modules	4
Installation, mounting	
Type of bottom connection for modular devices	biconnect
Dimensions	
Height	84 mm
Width	71 mm
Depth	70 mm
Use conditions	
Operating temperature	-25 - 40 °C
Storage/transport temperature	-55 - 70 °C
Connection	
Cross-section of input and output with screws, for flexible conductors	1 - 16 mm^2
Cross-section of input and output with screws, for massive conductors	1 - 25 mm^2
Use conditions	
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Sustainability	
RoHS conform	Yes