



GD110N

Mini-enclosure, gamma, 10 module, protect. class IP30, 1xPE, 1xN

Technical Features

Voltage

Nominal voltage 230 - 400 V

Installation, mounting

Suitable for outdoor usage No

Mounting on Surface mounting

Electric current

Rated current 63 A

Equipment

Number of rails 1

Number of rows 1

Number of section in width 1

With lock No

Has neutral terminal block Yes

Capacity

Number of modules 10

Functions

Has protection main switch No

With conduit inlets Yes

Dimensions

Height 180 mm

Width 218 mm

Depth 82 mm

Cover, door

Number of locks 0

Dimensions

Number of width units 10

Cover, door

Door/cover is transparent No

Connectivity

Mounting type Screw mounting

Materials

Material Plastic

RAL code 9010

Colour Pure white

Equipment

Has earthing terminal block Yes

Has mounting plate No

Safety

Protection class Isolation class II

Impact resistance IK IK05

Ingress Protection (IP) class IP30

Locking type Without lock

Glow wire test 750 °C

Sustainability

REACH-SVHC free Yes

RoHS conform Yes