



GD108B



**Mini-enclosure, gamma, 8 module, protect. class IP30**

**Technical Features**

**Voltage**

|                 |             |
|-----------------|-------------|
| Nominal voltage | 230 - 230 V |
|-----------------|-------------|

**Installation, mounting**

|             |                  |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

**Electric current**

|               |      |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

**Equipment**

|                            |    |
|----------------------------|----|
| Number of rails            | 1  |
| Number of rows             | 1  |
| With lock                  | No |
| Has neutral terminal block | No |

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 8 |
|-------------------|---|

**Dimensions**

|                       |        |
|-----------------------|--------|
| Height                | 180 mm |
| Width                 | 182 mm |
| Depth                 | 82 mm  |
| Number of width units | 8      |

**Cover, door**

|                           |    |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

**Materials**

|          |            |
|----------|------------|
| Material | Plastic    |
| RAL code | 9010       |
| Colour   | Pure white |

**Equipment**

|                             |    |
|-----------------------------|----|
| Has earthing terminal block | No |
| Has mounting plate          | No |

**Safety**

|                               |                    |
|-------------------------------|--------------------|
| Protection class              | Isolation class II |
| Impact resistance IK          | IK05               |
| Ingress Protection (IP) class | IP30               |
| Locking type                  | Without lock       |
| Glow wire test                | 750 °C             |

**Sustainability**

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |