



GD104T

Mini-enclosure, GD, 6 module wide, protect. class IP30, without door

Technical Features

Voltage

| | |
|-----------------|-------------|
| Nominal voltage | 230 - 230 V |
|-----------------|-------------|

Installation, mounting

| | |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

Electric current

| | |
|---------------|------|
| Rated current | 50 A |
|---------------|------|

Equipment

| | |
|----------------------------|----|
| Number of rails | 1 |
| Number of rows | 1 |
| With lock | No |
| Has neutral terminal block | No |

Capacity

| | |
|-------------------|---|
| Number of modules | 6 |
|-------------------|---|

Dimensions

| | |
|-----------------------|--------|
| Height | 180 mm |
| Width | 146 mm |
| Depth | 82 mm |
| Number of width units | 6 |

Cover, door

| | |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

Materials

| | |
|----------|------------|
| Material | Plastic |
| RAL code | 9010 |
| Colour | Pure white |

Equipment

| | |
|-----------------------------|----|
| Has earthing terminal block | No |
| Has mounting plate | No |

Safety

| | |
|-------------------------------|--------------------|
| Protection class | Isolation class II |
| Impact resistance IK | IK05 |
| Ingress Protection (IP) class | IP30 |
| Locking type | Without lock |
| Glow wire test | 750 °C |

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|