



FWB62N3

FWB encl.,univers,IP44,classII,96mod,interaxis 150mm,950x550x161mm

Technical Features

Installation, mounting

Mounting on Surface mounting

Electric current

Rated current 125 A

Equipment

Number of rails 10

Number of rows 10

Number of section in width 2

With lock No

Has neutral terminal block No

Capacity

Number of modules 96

Functions

With conduit inlets Yes

Dimensions

Height 950 mm

Width 550 mm

Depth 165 mm

Cover, door

Number of cabinet doors 1

Number of locks 1

Dimensions

Number of width units 24

Cover, door

Type of handle Hinged pattern handle

Door/cover is transparent No

Connectivity

Mounting type Surface mounting

Materials

Material Steel

RAL code 9010

Colour Pure white

Equipment

Has earthing terminal block No

Has mounting plate No

Safety

Protection class Isolation class II

Ingress Protection (IP) class IP44

Sustainability

RoHS conform Yes