



FWB62N3

FWB encl.,univers,IP44,classII,96mod,interaxis 150mm,950x550x161mm

### Technical Features

#### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

#### Electric current

Rated current	125 A
---------------	-------

#### Equipment

Number of rails	10
Number of rows	10
Number of section in width	2
With lock	No
Has neutral terminal block	No

#### Capacity

Number of modules	96
-------------------	----

#### Functions

With conduit inlets	Yes
---------------------	-----

#### Dimensions

Height	950 mm
Width	550 mm
Depth	165 mm

#### Cover, door

Number of cabinet doors	1
Number of locks	1

#### Dimensions

Number of width units	24
-----------------------	----

#### Cover, door

Type of handle	Hinged pattern handle
Door/cover is transparent	No

#### Connectivity

Mounting type	Surface mounting
---------------	------------------

#### Materials

Material	Steel
RAL code	9010
Colour	Pure white

#### Equipment

Has earthing terminal block	No
Has mounting plate	No

#### Safety

Protection class	Isolation class II
Ingress Protection (IP) class	IP44

#### Sustainability

RoHS conform	Yes
--------------	-----