

**Moulded Case Circuit Breaker h3 x160 TM FIX 3P3D 160A 40kA FTC**

**Technical Features**

**Electric current**

Rated current	160 A
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	40 kA
Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2	85 kA
Rated current 10°C according to IEC 60947	187.20 A
Rated current 15°C according to IEC 60947	184 A
Rated current 20°C according to IEC 60947	180.70 A
Rated current 25°C according to IEC 60947	177.40 A
Rated current 30°C according to IEC 60947	174.10 A
Rated current at 35°C according to IEC 60947	170.70 A
Rated current at 40°C according to IEC 60947	167.20 A
Rated current 45°C according to IEC 60947	163.60 A
Rated current 50°C according to IEC 60947	160 A
Rated current 55°C according to IEC 60947	156.20 A
Rated current at 60°C according to IEC 60947	152.40 A
Rated current 65°C according to IEC 60947	148.50 A
Rated current 70°C according to IEC 60947	144.40 A

**Architecture**

Number of poles	3
Control/operation element	Toggle
Device construction type	Fixed built-in
Neutral position	Without neutral

**Tripping**

Response time when opening	10 ms
----------------------------	-------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Voltage**

Rated impulse withstand voltage Uimp	8000 V
Rated insulation voltage Ui	690 V

**Functions**

Trip unit	TM F/F
-----------	--------

**Power**

Total power loss under IN	43.80 W
---------------------------	---------

**Endurance**

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

**Safety**

Ingress Protection (IP) class	IP4X
-------------------------------	------

**Connection**

Cross-section flexible conductor	4 - 70 mm <sup>2</sup>
Cross-section rigid conductor	4 - 95 mm <sup>2</sup>

**Installation, mounting**

Nominal tightening torque	6 - 6 Nm
Mounting-/Connection Position	Front

**Settings**

Thermal protection knob setting xIN	1
	1
Adjustment range short-term delayed short-circuit release	0 - 0 A

<b>Compatibility</b>	
Suitable for DIN Rail	No
<b>Main electrical attributes</b>	
Magnetic protection trip time	0 - 0 ms
<b>Sustainability</b>	
REACH-SVHC free	Yes
RoHS conform	Yes