



HDA016Z

Moulded Case Circuit Breaker h3 x160 TM FIX 3P3D 16A 18kA CTC

Technical Features

Electric current

Rated current I_N	16 A
Rated ultimate short-circuit breaking capacity I_{cu} under 400 V AC IEC 60947-2	18 kA
Rated ultimate short-circuit breaking capacity I_{cu} under 240 V AC IEC 60947-2	25 kA
Rated service breaking capacity I_{cs} under 230 V AC according to IEC 60947-2	25 kA
Rated service breaking capacity I_{cs} under 400 V AC according to IEC 60947-2	18 kA
Rated current at 10°C according to IEC 60947	21.50 A
Rated current at 15°C according to IEC 60947	20.90 A
Rated current at 20°C according to IEC 60947	20.20 A
Rated current at 25°C according to IEC 60947	19.60 A
Rated current at 30°C according to IEC 60947	18.90 A
Rated current at 35°C according to IEC 60947	18.20 A
Rated current at 40°C according to IEC 60947	17.50 A
Rated current at 45°C according to IEC 60947	16.70 A
Rated current at 50°C according to IEC 60947	16 A
Rated current at 55°C according to IEC 60947	15.10 A
Rated current at 60°C according to IEC 60947	14.20 A
Rated current at 65°C according to IEC 60947	13.30 A
Rated current at 70°C according to IEC 60947	12.30 A

Architecture

Number of poles	3
Neutral position	Without neutral

Tripping

Response time when opening	10 ms
----------------------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated impulse withstand voltage U_{imp}	8000 V
Rated insulation voltage U_i	690 V
Rated operational voltage U_e	220 - 415 V

Functions

Trip unit	TM F/F
-----------	--------

Power

Power dissipation at I_N	5.30 W
----------------------------	--------

Endurance

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Connection

Cross-section flexible conductor	4 - 70 mm ²
Cross-section rigid conductor	4 - 95 mm ²

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Settings

Thermal protection knob setting xIN	1
	1

Dimensions		
Height		130 mm
Width		75 mm
Depth		68 mm
Compatibility		
Suitable for DIN Rail		No
Main electrical attributes		
Magnetic protection trip time		0 - 0 ms
Sustainability		
REACH-SVHC free		Yes
RoHS conform		Yes