



20266089

## Thermostat, change-over contact, centre plate, Q.x, p. white velvety

### Technical Features

#### Architecture

Control/operation element	Rotative
---------------------------	----------

#### Electric current

Rated current	5 A
Max. switching current	10 A

#### Voltage

Nominal voltage	250 - 250 V
Rated voltage	250 V

#### Power supply

Supply voltage	230 V AC
----------------	----------

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Settings

Comfort temperature setpoint	5 - 30 °C
------------------------------	-----------

#### Materials

Colour	Polar white
RAL code	9010
Surface finish	Velvety
Material	Metal Plastic
Treatment	Untreated

#### Dimensions

Height	71 mm
Width	71 mm
Depth	47.50 mm

#### Screen

With display	No
--------------	----

#### Equipment

Switching temperature difference	0.50 K
Type of thermostat	Room thermostat
Type of probe	Bimetal
With heater	Yes

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Connection

Type of contacts	1x changeover
------------------	---------------

#### Use conditions

Energy efficiency class	I (1%)
-------------------------	--------

#### Texts

Installation mode	Without spreader claws
Type of connection	With plug-in terminals
Thermal re-circulation	With thermal return
Imprint	With imprint

#### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes