



20266086

Thermostat, change-over contact, centre plate, Q.x, ant. velvety, lacq.

Technical Features

Architecture

| | |
|---------------------------|----------|
| Control/operation element | Rotative |
|---------------------------|----------|

Electric current

| | |
|------------------------|------|
| Rated current | 5 A |
| Max. switching current | 10 A |

Voltage

| | |
|-----------------|-------------|
| Nominal voltage | 250 - 250 V |
| Rated voltage | 250 V |

Power supply

| | |
|----------------|----------|
| Supply voltage | 230 V AC |
|----------------|----------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Settings

| | |
|------------------------------|-----------|
| Comfort temperature setpoint | 5 - 30 °C |
|------------------------------|-----------|

Materials

| | |
|----------------|------------------|
| Colour | Anthracite |
| RAL code | 7016 |
| Surface finish | Velvety |
| Material | Metal Plastic |
| Treatment | Varnished |

Dimensions

| | |
|--------|----------|
| Height | 71 mm |
| Width | 71 mm |
| Depth | 47.50 mm |

Screen

| | |
|--------------|----|
| With display | No |
|--------------|----|

Equipment

| | |
|----------------------------------|-----------------|
| Switching temperature difference | 0.50 K |
| Type of thermostat | Room thermostat |
| Type of probe | Bimetal |
| With heater | Yes |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Connection

| | |
|------------------|---------------|
| Type of contacts | 1x changeover |
|------------------|---------------|

Use conditions

| | |
|-------------------------|--------|
| Energy efficiency class | I (1%) |
|-------------------------|--------|

Texts

| | |
|------------------------|------------------------|
| Installation mode | Without spreader claws |
| Type of connection | With plug-in terminals |
| Thermal re-circulation | With thermal return |
| Imprint | With imprint |

Sustainability

| | |
|-----------------|-----|
| Halogen free | Yes |
| REACH-SVHC free | Yes |
| RoHS conform | Yes |