



ST303

Bell transformer 8VA 230V 8-12V

Technical Features

Voltage

| | |
|------------------------------|-------------|
| Output voltage | 8 - 12 V |
| Rated operational voltage Ue | 230 - 230 V |
| Output voltage 2 | 12 V |

Capacity

| | |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

Power

| | |
|----------------------|------|
| Power consumption VA | 8 VA |
| Power | 8 VA |
| Power absorbed | 8 W |

Dimensions

| | |
|------------|-------------|
| Height | 111 mm |
| Width | 35 mm |
| Depth | 65 mm |
| Dimensions | 111 x 35 mm |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
| Temperature protection | Yes |

Equipment

| | |
|----------------------------|-----|
| Is short-circuit protected | Yes |
| On/off switch | No |

Voltage

| | |
|-----------------------------|--------|
| Rated insulation voltage Ui | 4000 V |
|-----------------------------|--------|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -20 - 35 °C |
|-----------------------|-------------|

Connection

| | |
|----------------------------------|-------------------|
| Cross-section flexible conductor | 4 mm ² |
| Cross-section rigid conductor | 6 mm ² |

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

Electric current

| | |
|--|--------|
| Intensity output 1 | 1 A |
| Intensity output 2 | 0.67 A |
| Rated secondary current (I _{sr}) | 1 A |

Installation, mounting

| | |
|---------------------------|----------------|
| Mounting on | DIN rail |
| Nominal tightening torque | 1.20 - 1.20 Nm |

Compatibility

| | |
|-----------------------|-----|
| Suitable for DIN Rail | Yes |
|-----------------------|-----|

Illustrations | Drawings

