



HIB463M

Motorized transfer switch 4P 1000A

Technical Features

Voltage

|                                          |             |
|------------------------------------------|-------------|
| Rated operational voltage U <sub>e</sub> | 380 - 415 V |
|------------------------------------------|-------------|

Electric current

|                                                                          |        |
|--------------------------------------------------------------------------|--------|
| Rated current                                                            | 1000 A |
| Rated conditional short-circuit current I <sub>cc</sub> with gl-gG fuses | 50 kA  |

Power

|                                            |          |
|--------------------------------------------|----------|
| Rated operational power under 400 V AC AC1 | 658000 W |
|--------------------------------------------|----------|

Architecture

|                          |                |
|--------------------------|----------------|
| Number of poles          | 4              |
| Device construction type | Fixed built-in |

Compatibility

|                                 |     |
|---------------------------------|-----|
| Suitable for DIN Rail           | No  |
| Suitable for distribution board | Yes |

Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Mounting plate |
|-------------|----------------|