



TRM693AU



Flush mounted radio output 3A 230V + 2 inputs mains powered

Technical Features

Connectivity

| | |
|---------------------------|-----------|
| Radio protocol | KNX Radio |
| Receiver category | 2 |
| With bus system KNX | No |
| With bus system KNX radio | Yes |

Dimensions

| | |
|----------------|------------|
| Dimensions | 40 x 40 mm |
| Height | 40 mm |
| Width | 40 mm |
| Depth | 20 mm |
| Built-in depth | 40 mm |

Electric current

| | |
|---------------|-----|
| Rated current | 3 A |
|---------------|-----|

Materials

| | |
|--------|------------|
| Colour | Light grey |
|--------|------------|

Equipment

| | |
|-------------------------------|-----|
| Radio frequency bidirectional | Yes |
| With switch for manual switch | Yes |

Frequency

| | |
|---------------------------|---------------|
| Frequency | 50 - 50 Hz |
| Radio reception frequency | 433 - 433 MHz |

Power

| | |
|-------------------------------------|-------|
| Output power | 690 W |
| 230 V incandescent and halogen lamp | 500 W |

Voltage

| | |
|--|-------------|
| Operating voltage | 230 - 230 V |
| Rated operational voltage U _e | 230 - 230 V |
| System supply voltage | 230 V AC |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -10 - 50 °C |
|-----------------------|-------------|

Connection

| | |
|----------------------------------|---------------------------|
| Cross-section rigid conductor | 0.5 - 2.5 mm ² |
| Cross-section flexible conductor | 0.5 - 1.5 mm ² |

Texts

| | |
|--------------------|---|
| Function | Reset function (to factory setting) |
| Installation mode | For installation behind flush-mounted inserts |
| Type of connection | With screw-in lift terminals |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|