



HDS078EC

**Moulded Case Circuit Breaker h3+ P160 TM FIX 1P1D 80A 18kA CTC**

**Technical Features**

**Electric current**

Rated current	80 A
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 240 V AC IEC 60947-2	18 kA
Rated service breaking capacity I <sub>cs</sub> under 230 V AC according to IEC 60947-2	18 kA
Rated current 10°C according to IEC 60947	106.90 A
Rated current 15°C according to IEC 60947	103.90 A
Rated current 20°C according to IEC 60947	100.90 A
Rated current 25°C according to IEC 60947	97.70 A
Rated current 30°C according to IEC 60947	94.40 A
Rated current at 35°C according to IEC 60947	91 A
Rated current at 40°C according to IEC 60947	87.50 A
Rated current 45°C according to IEC 60947	83.80 A
Rated current 50°C according to IEC 60947	80 A
Rated current 55°C according to IEC 60947	75.90 A
Rated current at 60°C according to IEC 60947	71.60 A
Rated current 65°C according to IEC 60947	67.10 A
Rated current 70°C according to IEC 60947	62.20 A

**Architecture**

Number of poles	1
Control/operation element	Toggle
Device construction type	Fixed built-in
Neutral position	Without neutral

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Voltage**

Rated impulse withstand voltage U <sub>imp</sub>	8000 V
Rated insulation voltage U <sub>i</sub>	800 V

**Functions**

Trip unit	TM F/F
-----------	--------

**Power**

Total power loss under I <sub>N</sub>	4.80 W
---------------------------------------	--------

**Endurance**

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

**Safety**

Ingress Protection (IP) class	IP4X
-------------------------------	------

**Installation, mounting**

Mounting-/Connection Position	Front
-------------------------------	-------

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Cover, door**

Interlockable	No
---------------	----

**Settings**

Thermal protection knob setting xI <sub>N</sub>	1
	1

---

**Dimensions**

Height	130 mm
Width	30 mm
Depth	68 mm

**Compatibility**

Compatible with RDC AOB	No
Suitable for DIN Rail	No

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes