



HDA018Z

**Moulded Case Circuit Breaker h3 x160 TM FIX 1P1D 20A 18kA CTC**

**Technical Features**

**Electric current**

Rated current	20 A
Rated ultimate short-circuit breaking capacity I <sub>cu</sub> under 240 V AC IEC 60947-2	18 kA
Rated service breaking capacity I <sub>cs</sub> under 230 V AC according to IEC 60947-2	18 kA
Rated current 10°C according to IEC 60947	25.40 A
Rated current 15°C according to IEC 60947	24.80 A
Rated current 20°C according to IEC 60947	24.20 A
Rated current 25°C according to IEC 60947	23.50 A
Rated current 30°C according to IEC 60947	22.80 A
Rated current at 35°C according to IEC 60947	22.20 A
Rated current at 40°C according to IEC 60947	21.40 A
Rated current 45°C according to IEC 60947	20.70 A
Rated current 50°C according to IEC 60947	20 A
Rated current 55°C according to IEC 60947	19.20 A
Rated current at 60°C according to IEC 60947	18.30 A
Rated current 65°C according to IEC 60947	17.50 A
Rated current 70°C according to IEC 60947	16.60 A

**Architecture**

Number of poles	1
Control/operation element	Toggle
Device construction type	Fixed built-in
Neutral position	Without neutral

**Tripping**

Response time when opening	10 ms
----------------------------	-------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Voltage**

Rated impulse withstand voltage U <sub>imp</sub>	8000 V
Rated insulation voltage U <sub>i</sub>	690 V
Rated operational voltage U <sub>e</sub>	220 - 240 V

**Functions**

Trip unit	TM F/F
-----------	--------

**Power**

Total power loss under I <sub>N</sub>	2.70 W
---------------------------------------	--------

**Endurance**

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

**Safety**

Ingress Protection (IP) class	IP4X
-------------------------------	------

**Connection**

Cross-section flexible conductor	6 - 70 mm <sup>2</sup>
Cross-section rigid conductor	6 - 95 mm <sup>2</sup>

**Installation, mounting**

Nominal tightening torque	6 - 6 Nm
Mounting-/Connection Position	Front

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

<b>Cover, door</b>	
Interlockable	Yes
<b>Settings</b>	
Thermal protection knob setting xIN	1
	1
<b>Cable</b>	
Cable material	Copper
<b>Dimensions</b>	
Height	130 mm
Width	25 mm
Depth	68 mm
<b>Compatibility</b>	
Suitable for DIN Rail	Yes
<b>Installation, mounting</b>	
Nominal tightening torque down terminal	6 - 6 Nm
Nominal tightening torque top terminal	6 - 6 Nm
<b>Main electrical attributes</b>	
Magnetic protection trip time	0 - 0 ms
<b>Sustainability</b>	
REACH-SVHC free	Yes
RoHS conform	Yes