



WNA025



IP55



cubyko PB 1F w. FPL compos. grey

Technical Features

Electric current

Momentary contact current 10 A

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 60 Hz

Architecture

Control/operation element Rocker

Materials

Colour Grey

Surface finish Matt
Satin finish

Material Thermoplastic

Treatment Untreated

Transparent No

Dimensions

Height 70.90 mm

Width 70.90 mm

Depth 41.50 mm

Built-in depth flush-mounted boxes 40 mm

Height of P-touch band for labelling field 12 mm

Installation, mounting

Mounting on Flush mounting
Surface mounting

Controls and indicators

Number of buttons 1

Type of push button Single push button

With feedback signal contact No

Connection

Connector/plug type Turn screw lock

Safety

Ingress Protection (IP) class IP55

Impact resistance IK IK05

Accessories

Has labelling field Yes

Use conditions

Operating temperature -25 - 35 °C

Texts

Imprint With imprint

Installation mode For screw fastening

Lighting With blue 230 V LED unit

Terminal Wago clip-in 3-wire connection terminal for wiring

Type of connection With N-terminal
With plug-in terminals

Suitable for

cubyko

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes
