



HMT051DR

Moulded Case Circuit Breaker h3+ P250 TM ADJ 4P4D N0-100% 50A 50kA FTC

Technical Features

Electric current

Rated current	50 A
Rated ultimate short-circuit breaking capacity I _{cu} under 400 V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity I _{cu} under 240 V AC IEC 60947-2	65 kA
Rated service breaking capacity I _{cs} under 230 V AC according to IEC 60947-2	65 kA
Rated service breaking capacity I _{cs} under 400 V AC according to IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity I _{cu} under 660 V AC IEC 60947-2	6 kA
Rated ultimate short-circuit breaking capacity I _{cu} under 690 V AC IEC 60947-2	6 kA
Rated current 10°C according to IEC 60947	63.10 A
Rated current 15°C according to IEC 60947	61.60 A
Rated current 20°C according to IEC 60947	60.10 A
Rated current 25°C according to IEC 60947	58.50 A
Rated current 30°C according to IEC 60947	56.90 A
Rated current at 35°C according to IEC 60947	55.30 A
Rated current at 40°C according to IEC 60947	53.60 A
Rated current 45°C according to IEC 60947	51.80 A
Rated current 50°C according to IEC 60947	50 A
Rated current 55°C according to IEC 60947	48.10 A
Rated current at 60°C according to IEC 60947	46.20 A
Rated current 65°C according to IEC 60947	44.10 A
Rated current 70°C according to IEC 60947	42 A

Architecture

Number of poles	4
Control/operation element	Toggle
Device construction type	Fixed built-in
Neutral position	Left

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated impulse withstand voltage U _{imp}	8000 V
Rated insulation voltage U _i	800 V
Rated operational voltage U _e	220 - 690 V

Functions

Trip unit	TM A/A
-----------	--------

Power

Total power loss under I _N	15 W
---------------------------------------	------

Endurance

Electric endurance in number of cycles	10000
Number of mechanical operations	40000

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Connection

Cross-section flexible conductor	35 - 150 mm ²
Cross-section rigid conductor	35 - 185 mm ²

Cover, door

Interlockable	Yes
---------------	-----

Settings

Thermal protection knob setting xI _N	0.63
	0.8
	1

Cable

Cable material	Copper Aluminium
----------------	---------------------

Compatibility

Compatible with RDC AOB	Yes
Suitable for DIN Rail	No
Suitable for distribution board	Yes

Dimensions

Dimensions	165 x 140 mm
Height	165 mm
Width	140 mm
Depth	97 mm
Downstream busbar: width, height, diameter screw (max.)	4 mm 8.5 mm 25 mm
Top stream busbar: width, height, diameter screw (max.)	4 mm 8.5 mm 25 mm

Installation, mounting

Mounting-/Connection Position	Front
Nominal tightening torque	12 - 12 Nm
Nominal tightening torque down terminal	12 - 12 Nm
Nominal tightening torque top terminal	12 - 12 Nm

Electrical protection

Instantaneous protection (li): dial setting coefficient	6 8 10 13
---	--------------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes